



Pressure sensors

Handling guideline, pressure sensor dies

Series/Type:
Ordering code:

Date: 2016-02-04
Version: 1

© EPCOS AG 2016. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

Pressure sensors

Handling guideline, pressure sensor dies

Introduction

This application note is intended as a customer's guideline for handling bare pressure sensor dies. Improper handling can impair the performance of the elements. This document provides information about the appropriate handling of the pressure sensor dies.

Delivery form

For delivery, dies are packaged either on a tape or in waffle packs, referred to as trays in the following document.

For each die type there is a particular tray type with corresponding pocket dimensions. The tray stack (Fig. 1) is packed in a labelled spring box (Fig. 2).



Figure 1



Figure 2

These spring boxes are in turn packed in a plastic tray (Fig. 3) and sealed in an antistatic bag (Fig. 4).



Figure 3



Figure 4

The tape with dies is stabilized with a labelled frame shipper (Fig. 5), which is sealed in an antistatic bag (Fig. 6).



Figure 5



Figure 6

Sensitivity

The delivered dies have undergone electrical and optical inspection upon shipment. This ensures that their performance conforms with the specification and that they are free of any damage or contamination.

- **Contamination** during handling, for example, particles on bond pads and semiconductor surfaces can affect the performance of a die. For this reason dies must be processed in a class 1000 clean room (ISO 6) and handled with clean tools.
- Any **mechanical damage** can also be crucial for the performance of the die. Bending forces can cause cracks. Therefore, only a limited mechanical pressure should be applied on the die and its active side (top side with wire bond pads) should never be touched. Appropriate tools are indispensable during handling.
- The die is susceptible to **electric fields**. The environment must be electrostatically protected according to relevant electrostatic discharge (ESD) guidelines when processing the die. Thus, each device or tool that comes into contact with the die should be adjusted on the same electric potential as the die.

Handling requirements

- In order to avoid contamination, the active side of the bare die should never be touched, nor should the die be contacted by bare fingers. Packaged dies should be opened only in a clean room in order to prevent any dust from coming into contact with the surface of the dies. Handling tools must be cleaned regularly and properly to prevent residues from transferring to the surface of dies. Please contact your equipment supplier for cleaning instructions.
- Mechanical pressure applied at any stage to the die should be minimized. Suitable tools for picking dies from the front side should be equipped with a soft rubber tip with a vacuum hole in the middle that is larger than the diaphragm of the sensor die. Pushing up the dies from the tape can be done with ejector pins with multiple needles. Some tools such as tweezers can damage the dies. The dies should be transported only in appropriate boxes and bags. The forces applied during die bonding processes should be kept below 100 cN in order to keep mechanical stress at a minimum. It is recommended to reduce overall handling to a minimum.
- Process temperatures should be kept as low as possible in order to prolong the stability and lifetime of the die. A temperature of +225 °C should not be exceeded.

Mounting instructions

The assembly process can affect the performance of the die considerably with regards to hysteresis behavior of different parameters as well as long-term drift.

- Mechanical stress during the assembly process is the main factor that negatively affects the performance. A soft silicone adhesive with low hardness (shore A approx. 30) and adhesive thickness $>50\ \mu\text{m}$ is recommended. (Hard adhesives such as epoxy could result in an offset drift and higher temperature coefficient of offset voltage).
- Adhesives or its residues on the diaphragm can result in a high temperature dependency and high long-term drifts of the output signal.
- Bond pads consist of aluminum or gold, depending on the application or requirements.
- Aluminum wires (only aluminum bond pads) or gold wires can be used for wire bonding.
- Gel can be applied to the sensor surface in order to protect the bond pads from corrosion. Please note that gel can influence the diaphragm mechanically and therefore also the output characteristic.

Storage conditions

Any parts not being used in processing must be protected according to JEDEC JESD 625 B. Any packaging materials used for this purpose must be non-outgassing and chemically stable. Furthermore, the following storage conditions should be preserved (except as noted otherwise):

Storage in cabinets (if shipment package is opened):

- Atmosphere: inert gas, dry air or dry nitrogen
- Temperature range (in cabinet): $20 \pm 3\ \text{°C}$
- Relative humidity range (in cabinet): $< 40\%$
- Particle count (in cabinet): Class 6 per ISO 14644:1999 (equivalent FED STD 209E Class 1000)
- Shelf life under these conditions: 24 months for deliveries in trays
- Shelf life under these conditions: 12 months for deliveries on tape

Storage in containers (if shipment package is sealed):

- Sealed as delivered or backfilled with inert gas, dry air or dry nitrogen and re-sealed
- Temperature range: $20 \pm 3\ \text{°C}$
- Relative humidity range: $< 50\%$
- Particle count (during backfill): Class 6 per ISO 14644:1999 (equivalent FED STD 209E Class 1000)
- Shelf life for deliveries in trays under these conditions: 12 months
- Shelf life for deliveries on tape under these conditions: 6 months

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, Alu-X, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PQSine, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, TFAP, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.